

プッシュプルゲージ

PUSH-PULL GAGE

Success

■ MODEL-AWF

■ MODEL-ANF

■ MODEL-AWF/C

■ MODEL-AEF



PUSH-PULL GAGE

Success


Manufactured by M.H.M CO.,LIMITED



Manufactured by M.H.M CO.,LIMITED

PUSH-PULL GAGE

Manufactured by M.H.M CO., LIMITED



This rugged mechanical push-pull force gage is designed for easy, stable and accurate measurement of tension and compression, and peak force hold mechanism is built in with easy-to-read dial graduation. Dial graduation is 100 lines excepting 30N, 300N (or 3kgf, 30kgf) which is 120 lines. Accuracy is guaranteed within 0.5%FS (full scale) and maximum stroke is 10mm. Premium quality reinforced plastic body is designed to fit human's hand and test stand. Net weight is 530gs.

海外用機種

MODEL-ANF

容量: 1kgf~50kgf
10N~500N

Capacity: 1kgf~50kgf
10N~500N

Tension/Compression



- 本器はN単位とkgf単位との2重目盛です。
- These models have dual graduations in unit of N and kgf.

Model	Capacity	Min. Reading	Capacity	Min. Reading	Stroke
ANF-10	10N	0.1N	1kgf	10gf	10mm
ANF-20	20N	0.2N	2kgf	20gf	10mm
ANF-30	30N	0.2N	3kgf	25gf	10mm
ANF-50	50N	0.5N	5kgf	50gf	10mm
ANF-100	100N	1N	10kgf	100gf	10mm
ANF-200	200N	2N	20kgf	200gf	10mm
ANF-300	300N	2N	30kgf	300gf	10mm
ANF-500	500N	5N	50kgf	500gf	10mm



MODEL-AEF

● 本器はkgf専用です。(kgf unit only)

容量: 1kgf~50kgf

Capacity: 1kgf~50kgf

Tension/Compression



Model	Capacity	Minimum Reading	Stroke
AEF-1	1kgf	10gf	10mm
AEF-2	2kgf	20gf	10mm
AEF-3	3kgf	25gf	10mm
AEF-5	5kgf	50gf	10mm
AEF-10	10kgf	100gf	10mm
AEF-20	20kgf	200gf	10mm
AEF-30	30kgf	250gf	10mm
AEF-50	50kgf	500gf	10mm



標準付属品



- 30N(3Kgf) の機種以下のアタッチメントはアルミ製品になります。
- Attachment tools for 30N(3kgf) and under are made of aluminum.


アフターサービス

- 当社の設計上および製造上の故障については、
1 年間無償にて修理または交換させていただきます。
トレサビリティおよび修理、校正、荷重検定、
書類作成については、当社までお問い合わせ下さい。




トレサビリティ書類

上面図



- 本器の取付け穴図
- A fixed method of a push-pull gage.

取付け穴図



- 図の 4 本の M3 のネジを取り外し、機械の取り付けベースに共締して下さい。
- Take out 4 pieces of screw (M3) shown in the drawing and fix them to the plate on machine.



有限会社 **M.H.M**

〒559-0033
 大阪市住之江区南港中4丁目2番13-909
 TEL:06-6569-3030 FAX:06-6569-3033
 E-mail:mizukami@ra2.so-net.ne.jp

Manufactured by M.H.M CO.,LIMITED

Address : 4-2-13-909,Nankonaka,Suminoe-Ku,
 Osaka,Japan 559-0033

Tel:+81-6-6569-3030 Fax:+81-6-6569-3033

製造元

代理店